

The following guidelines are designed to provide an accurate and complete list of components necessary to complete your panel railing system. This checklist and our Linear Collection Metal Panel Systems brochure will provide the flexibility to comply with most building codes as they relate to handrail height and infill spacing requirements. The following guidelines are designed for stairways with 7 1/2" rise and 10" run (approx 36.9°), a rake handrail height of 36" and level handrail heights between 36" and 43" (depending on handrail used, curb wall height, amount panels are elevated, etc.). All metal panel lengths are plan view measurements. All products are for interior use only. **Consult your local building code official before purchasing and installing this system. For interior use only.**

Item	Guidelines	Part #	Qty.
1 TREADS	Select one tread for each step. If false treads are utilized, select one or two per tread depending on application.		
2 LANDING TREAD	Select sufficient lineal footage of LJ-8890-5 for the entire balcony and width of stairs at each landing. Custom landing tread can also be quoted and ordered.		
3 COVE MOULD	Select sufficient lineal footage of LJ-8895 to go under all landing tread. (For level runs and stairs with risers)		
4 RAKE PANELS	<p>Open Tread Stairways: Select the appropriate sizes and quantity of open tread stair panels to fill the plan view layout of the open tread stairway rake. Spaces between panels can be no more than 4". Be sure to take into consideration the 1/2" thickness of each Panel Post and 1" thickness of each Spacer Newel (see 6 & 7 below) when calculating the spacing. Select from the following rake panels: (sizes indicated are plan view widths) PR-O1236 (12"), PR-O1836 (18"), PR-O2436 (24"), PR-O3036 (30"), PR-O3636 (36")</p> <p>Kneewall Stairways: Select the appropriate sizes and quantity of kneewall stair panels to fill the plan view layout of the kneewall stairway rake. Spaces between panels can be no more than 4". Be sure to take into consideration the 1" thickness of each Spacer Newel if used (see 7 below) when calculating the spacing. Select from the following rake panels: (sizes indicated are plan view widths) PR-K1236 (12"), PR-K1836 (18"), PR-K2436 (24"), PR-K3036 (30"), PR-K3636 (36")</p>		
5 LEVEL RUN PANELS	<p>Elevated Panels: Select the appropriate sizes and quantity of panels to fill the plan view layout of each level run. Spaces between panels can be no more than 4". Be sure to take into consideration the 1/2" thickness of each Panel Post and 1" thickness of each Spacer Newel (see 6 & 7 below) when calculating the spacing. Select from the following level panels for a 39" level rail height: PL-CE1239 (12"), PL-CE1839 (18"), PL-CE2439 (24"), PL-CE3039 (30"), PL-CE3639 (36"), PL-CE4239 (42"), PL-CE4839 (48"). Select from the following level panels for a 43" level rail height: PL-CE1243 (12"), PL-CE1843 (18"), PL-CE2443 (24"), PL-CE3043 (30"), PL-CE3643 (36"), PL-CE4243 (42"), PL-CE4843 (48")</p> <p>Curb Wall Panels: Select the appropriate sizes and quantity of panels to fill the plan view layout of each level run. Spaces between panels can be no more than 4". Be sure to take into consideration the 1" thickness of each Spacer Newel if used (see 7 below) when calculating the spacing. Select from the following level panels for a 39" level rail height: PL-CE1239 (12"), PL-CE1839 (18"), PL-CE2439 (24"), PL-CE3039 (30"), PL-CE3639 (36"), PL-CE4239 (42"), PL-CE4839 (48"). Select from the following level panels for a 43" level rail height: PL-CE1243 (12"), PL-CE1843 (18"), PL-CE2443 (24"), PL-CE3043 (30"), PL-CE3643 (36"), PL-CE4243 (42"), PL-CE4843 (48")</p> <p>Flush Mount Panels: Select the appropriate sizes and quantity of panels to fill the plan view layout of each level run. Spaces between panels can be no more than 4". Be sure to take into consideration the 1" thickness of each Spacer Newel if used (see 7 below) when calculating the spacing. Select from the following level panels for a 36" level rail height: PL-F1236 (12"), PL-F1836 (18"), PL-F2436 (24"), PL-F3036 (30"), PL-F3636 (36"), PL-F4236 (42"), PL-F4836 (48"). Select from the following level panels for a 39" level rail height: PL-F1239 (12"), PL-F1839 (18"), PL-F2439 (24"), PL-F3039 (30"), PL-F3639 (36"), PL-F4239 (42"), PL-F4839 (48").</p>		
6 PANEL POSTS	<p>Panel Posts are used on open tread stairways and elevated panel level runs. Select 2 Panel Posts with 2-Hole Foot Plate (P-POST2H) per panel. The Panel Post with 4-Hole Foot Plate (P-POST4H) is often used at the end of a level run that ends near a wall.</p> <p>NOTE: A Panel Post kit is available that includes: 2 Panel Posts with 2-Hole Foot Plate (P-POST2H), 4 Post Foot Lag Screws (P-POSTFTSCR2.75) and 6 Post and Barrel Bolts (P-POSTBOLT1.0).</p>		
7 SPACER NEWELS	<p>Spacer newels must be used in any space between panels that is over 4" to comply with building codes. Also, rake and level runs cannot exceed 15' without a spacer newel.</p> <p>Kneewall Stairways: Select the necessary quantity of Kneewall Spacer Newels (PR-K36NWL2H).</p> <p>Level Run Elevated Panels: Select the necessary quantity of Level Spacer Newels. For a 39" level rail height: PL-E39NWL4H. For a 43" level rail height: PL-E43NWL4H</p> <p>Level Run Curb Wall Panels: Select the necessary quantity of Level Spacer Newels. For a 39" level rail height: PL-C39NWL4H. For a 43" level rail height: PL-C43NWL4H</p> <p>Level Run Flush Mount Panels: Select the necessary quantity of Level Spacer Newels. For a 36" level rail height: PL-F36NWL4H. For a 39" level rail height: PL-F39NWL4H</p>		
8 HARDWARE	Every rake and level panel comes with screws for attachment to the handrail. Screws are also included for the bottom of each panel (use for level flush mount, level curb wall mount and kneewall stair applications only). Spacer newels and panel posts include post foot lag screws. Spacer newels also include screws for attachment to the handrail. Each panel post includes 3 panel post and barrel fasteners. The panel post kit includes 6 panel post and barrel fasteners and 4 post foot lag screws. Each of these hardware items are also available separately, if needed. See pages 2 & 4 of the Metal Panel Systems brochure.		
9 HANDRAIL	Select 684 handrail at a rate of 13' per each tread and include enough for all level runs and walls (if wall rail is required). Handrail is available in 8', 10', 12', 14', & 16' lengths.		
10 HANDRAIL GOOSENECK FITTINGS	A gooseneck handrail fitting must be used for the following rake to level run transitions: 36" rake to 39" level; 36" rake to 42" level; 39" rake to 42" level. Select the appropriate gooseneck fitting: 784LHGN (Left Hand Gooseneck), 784RHGN (Right Hand Gooseneck), 784SGN (Straight Gooseneck)		
11 HANDRAIL FITTINGS (Miscellaneous Components)	Select the necessary Overeasing, Upeasing and Level Quarterturns as needed for changes in elevation and/or direction of the handrail. If continuous handrail is needed to transition from the rake, around a wall, and continue up the stair as wall rail, select two Level Quarterturns. Select from these fittings: 784OE (Overeasing), 784UE (Upeasing), 784QTR (Level Quarterturn)		